

Scope Electric

Manufacturer of professional milk analyzers

MilkoScope

Exports World Wide

Julie C2 Automatic



Specification

Case – Aluminum 2 mm

LED display

Possibility for work at 12V, powered by a car battery with a cable, included in the analyzer's kit.

Built-in device for coping with distortions, caused by electricity malfunctions.

PC connection option with a cable and software, included in the analyzer's kit. Thermal printer connection option – to be chosen by the client.

The milk analyzer has 3 calibration channels, which can be set for 3 types of milk, chosen by the client.

One calibration is included in the analyzer's price, the other/s should be paid.

Cleaning – manual, with a cleaning device, included in the analyzer's kit and the MilkoScope – Flush cleaning concentrate.

Written and sound message for necessity of cleaning.

MilkoScope Julie C2 is a mobile milk analyzer, suitable for milk collecting centers. It is a decision for all problems at the milk

producer's place, as well as at farms, laboratories and small milk processing enterprises.

Suitable for all types of animal milk.

Scope Electric Bulgaria
Razgrad
Phone/Fax: +359-84-660-654
Mobile: +359-888-89-10-89
E-mail: office@scope-electric.com
www.scope-electric.com

Scope Electric Germany
Regensburg
Phone: +49-941-690-7945
Mobile: +49-1797532699
E-mail: office.de@scope-electric.com
www.scope-electric.com

Scope Electric

Manufacturer of professional milk analyzers

MilkoScope

Measuring Ranges:		Technical Overview:	
Fat:	0% - 12%	Sample Volume:	10 ml.
Protein:	0% - 7%	Sample Speed:	70 sec.
Lactose:	0% - 7%	Sample Temperature:	5 - 30°C
Solids-Non-Fat (SNF):	0% - 15%	Humidity:	0 - 80% RH
Density:	1000-1200 kg/m3	Database Processing:	RS 232 port
Added Water:	0% - 100%	Power Supply:	110/230VAC±10%,50/60Hz
Sample Temperature:	5 - 30°C	Power Consumption:	25W
		Dimension:	H=280 mm,W=135 mm,D=265 mm
		Weight:	2,9 kg

Accuracy:			Kit:	
Fat:	±0.05%	against Rose Gottlieb	Milk Analyzer	
Protein:	±0.05%	against Kjeldahl	Power Supply Cable 220V	
Lactose:	±0.05%	against Polarimetry	Serial Cable to PC	1 piece
Solids-Non-Fat (SNF):	±0.08%	against Drying Oven	Sample Cup	1 piece
Density:	±0,3 kg/m3	against Gravimetric	Spare Hose	1 piece
Added Water:	±3%	against pycnometer	Cleaning Concentrate	1 piece
		against cryoscope	User's Manual	1 piece
			CD with software	

Scope Electric Bulgaria
Razgrad
Phone/Fax: +359-84-660-654
Mobile: +359-888-89-10-89
E-mail: office@scope-electric.com
www.scope-electric.com

Scope Electric Germany
Regensburg
Phone: +49-941-690-7945
Mobile: +49-1797532699
E-mail: office.de@scope-electric.com
www.scope-electric.com