

Scope Electric

Manufacturer of professional milk analyzers

MilkoScope

Exports World Wide

Julie C5 Automatic



Specification

Professional-class milk analyzer. In our clients' opinion, working with Julie C5 Automatic is pleasure.

Case – Aluminum 3 mm

LCD display, 4 rows, 20 symbols

Scope – system for automatic start of the analysis

Built-in device for coping with distortions, caused by electricity malfunctions.

System for control of the sound signal.

PC connection option with a cable and software, included in the analyzer's kit.

Built-in thermal printer, which prints out the values of all measured parameters. It can be turned off.

The milk analyzer has 3 calibration channels, which can be set for 3 types of milk, chosen by the client.

One calibration is included in the analyzer's price – the other/s should be paid.

Written and sound message for necessity of cleaning.

Cleaning – automatic, with the MilkoScope – Flush cleaning concentrate.

Julie C5 Automatic is suitable for work in laboratories of big milk processing companies, as well as in certified laboratories.

It can be used for analysis of all types of animal milk, as well as for soy milk.

Scope Electric Bulgaria

Razgrad

Phone/Fax: +359-84-660-654

Mobile: +359-888-89-10-89

E-mail: office@scope-electric.com

www.scope-electric.com

Scope Electric Germany

Regensburg

Phone: +49-941-690-7945

Mobile: +49-1797532699

E-mail: office.de@scope-electric.com

www.scope-electric.com

Scope Electric

Manufacturer of professional milk analyzers

MilkoScope

Measuring Ranges:		Technical Overview:	
Fat:	0% - 20%	Sample Volume:	5-15 ml.
Protein:	0% - 15%	Sample Speed:	60 sec.
Lactose:	0% - 20%	Sample Temperature:	5 - 30°C
Solids-Non-Fat (SNF):	0% - 20%	Humidity:	0 - 80% RH
Solids:	0% - 10%	Database Processing:	RS 232 port
Density:	1000-1200 kg/m3	Power Supply:	110/230VAC±10%,50/60Hz
Added Water:	0% - 100%	Power Consumption:	40W
Freezing Point:	-0,400 to -0,700°C	Dimension:	H=310 mm,W=270 mm,D=180 mm
Sample Temperature:	5 - 30°C	Weight:	3,7 kg

Accuracy:			Kit:	
Fat:	±0.02%	against Rose Gottlieb	Milk Analyzer	
Protein:	±0.02%	against Kjeldahl	Power Supply Cable 220V	
Lactose:	±0.02%	against Polarimetry	Serial Cable to PC	1piece
Solids-Non-Fat (SNF):	±0.05%	against Drying Oven	RS 232 Cable	1piece
Solids:	±0.02%	against Gravimetric	Thermal Printer Paper Roll	1piece
Density:	±0,3 kg/m3	against pycnometer	Sample Cup	1piece
Added Water:	±1%	against cryoscope	Waste Container	1piece
Freezing Point:	0,005 °C		Spare Hose	1piece
			Cleaning Concentrate	
			User's Manual	
			CD with software	

Scope Electric Bulgaria
Razgrad
Phone/Fax: +359-84-660-654
Mobile: +359-888-89-10-89
E-mail: office@scope-electric.com
www.scope-electric.com

Scope Electric Germany
Regensburg
Phone: +49-941-690-7945
Mobile: +49-1797532699
E-mail: office.de@scope-electric.com
www.scope-electric.com